

| Item                 | Description                    | Compliant     |     |
|----------------------|--------------------------------|---------------|-----|
| 5TC-GG-K-36-36       | GLASS INSULATED T/C'S 5/PK     | YES           |     |
| BB-SMP-CR062-100     | CRIMPSTYLE BRASSBUSHING-100SET | YES           |     |
| BS12A                | BARRIER STRIP ROHS             | YES           |     |
| BS16A                | BARRIER STRIP ROHS             | YES           |     |
| BS20A                | BARRIER STRIP ROHS             | YES           |     |
| BS2A                 | BARRIER STRIP ROHS             | YES           |     |
| BS4A                 | BARRIER STRIP ROHS             | YES           |     |
| BS6A                 | BARRIER STRIP ROHS             | YES           |     |
| BS8A                 | BARRIER STRIP ROHS             | YES           |     |
| BSJ-E                | VIOLET WITH LUGS 6/PK.         | YES           |     |
| BSJ-J                | BLACK WITH LUGS 6/PK.          | YES           |     |
| BSJ-K                | YELLOW WITH LUGS 6/PK.         | YES           |     |
| BSJ-N                | ORANGE WITH LUGS 6/PK.         | YES           |     |
| BSJ-R/S              | GREEN WITH LUGS 6/PK.          | YES           |     |
| BSJ-T                | BLUE WITH LUGS 6/PK.           | YES           |     |
| BSJ-U                | WHITE WITH LUGS 6/PK.          | YES           |     |
| DRTB-E-2             | THERMOCOUPLE TB TYPE E W/FEM   | YES           |     |
| DRTB-J-2             | THERMOCOUPLE TB TYPE J W/FEM   | YES           |     |
| DRTB-K-2             | THERMOCOUPLE TB TYPE K W/FEM   | YES           |     |
| DRTB-N-2             | THERMOCOUPLE TB TYPE N W/FEM   | YES           |     |
| DRTB-R/S-2           | THERMOCOUPLE TB TYPE R/S W/FEM | YES           |     |
| DRTB-T-2             | THERMOCOUPLE TB TYPE T W/FEM   | YES           |     |
| DRTB-U-2             | THERMOCOUPLE TB TYPE U W/FEM   | YES           |     |
| DTC-E-F              | DUAL ELEMENT CONNECTOR,PURPLE  | YES           |     |
| DTC-E-M              | DUAL ELEMENT CONNECTOR,PURPLE  | YES           |     |
| DTC-J-F              | DUAL ELEMENT CONNECTOR,BLACK   | YES           |     |
| DTC-J-M              | DUAL ELEMENT CONNECTOR,BLACK   | YES           |     |
| DTC-K-F              | DUAL ELEMENT CONNECTOR,YELLOW  | YES           |     |
| DTC-K-M              | DUAL ELEMENT CONNECTOR,YELLOW  | YES           |     |
| DTC-N-F              | DUAL ELEMENT CONNECTOR,ORANGE  | YES           |     |
| DTC-N-M              | DUAL ELEMENT CONNECTOR,ORANGE  | YES           |     |
| DTC-R/S-F            | DUAL ELEMENT CONNECTOR,GREEN   | YES           |     |
| DTC-R/S-M            | DUAL ELEMENT CONNECTOR,GREEN   | YES           |     |
| DTC-T-F              | DUAL ELEMENT CONNECTOR,BLUE    | YES           |     |
| DTC-T-M              | DUAL ELEMENT CONNECTOR,BLUE    | YES           |     |
| DTC-U-F              | DUAL ELEMENT CONNECTOR,WHITE   | YES           |     |
| DTC-U-M              | DUAL ELEMENT CONNECTOR,WHITE   | YES           |     |
| EXPP-T-20S-TCB-P-500 | SHIELDED T/C EXTENSION CABLE   | YES           |     |
| GG-K-36-500          | INSULATED T/C WIRE             | YES           |     |
| HACL                 | MOUNTING BRACKET               | YES           |     |
| HTCL                 | SAFETY CLIPS-NHX (10/PKG)      | YES           |     |
| MBS-02               | BEZEL MOUNTING STRIP           | YES           |     |
| MPJ-J-F              | SUB-MINI PANEL JACK,BLACK      | YES           |     |
| MPJ-K-F              | SUB-MINI PANEL JACK,YELLOW     | YES           |     |
| MPJ-R/S-F            | SUB-MINI PANEL JACK,GREEN      | YES           |     |
| MPJ-T-F              | SUB-MINI PANEL JACK,BLUE       | YES           |     |
| MPJ-U-F              | SUB-MINI PANEL JACK,WHITE      | YES           |     |
| MRB                  | PROTECTIVE COVER FOR SMP CONN  | YES           |     |
| MRB                  | PROTECTIVE COVER FOR SMP CONN  | YES           |     |
| MRBS                 | SMP HI-TEMP BOOT, GRAY         | YES           |     |
| MSS-02               | MPJ SNAP STRIP                 | YES           |     |
| MTC-5-FC             | FEMALE CORD CONNECTOR          | NOT COMPLIANT | 非対応 |
| MTC-5-FF             | FEMALE BULKHEAD CONNECTOR      | NOT COMPLIANT | 非対応 |
| MTC-5-MC             | MALE CORD CONNECTOR            | NOT COMPLIANT | 非対応 |
| MTC-AL-P             | MALE PIN                       | YES           |     |
| MTC-AL-S             | SOCKET (FEMALE)                | YES           |     |
| MTC-CH-P             | MALE PIN                       | YES           |     |
| MTC-CH-S             | SOCKET (FEMALE)                | YES           |     |
| MTC-CO-P             | MALE PIN                       | YES           |     |
| MTC-CO-S             | SOCKET (FEMALE)                | YES           |     |
| MTC-IR-P             | MALE PIN                       | YES           |     |
| MTC-IR-S             | SOCKET (FEMALE)                | YES           |     |
| MTC-IT               | TOOLS                          | NOT COMPLIANT | 非対応 |
| MTC-RT               | MTC REMOVAL TOOL               | YES           |     |

| Item             | Description                            | Compliant |
|------------------|--|-----------|
| MTP-E-M          | MINI THREE PRONG,PURPLE                | YES       |
| MTP-J-M          | MINI THREE PRONG,BLACK                 | YES       |
| MTP-K-M          | MINI THREE PRONG,YELLOW                | YES       |
| MTP-N-M          | MINI THREE PRONG,ORANGE                | YES       |
| MTP-T-M          | MINI THREE PRONG,BLUE                  | YES       |
| MTP-U-M          | MINI THREE PRONG,WHITE                 | YES       |
| NHX-K-F          | HI TEMP CONNECTOR,YELLOW               | YES       |
| NHX-K-M          | HI TEMP CONNECTOR,YELLOW               | YES       |
| NHX-N-F          | HI TEMP CONNECTOR,ORANGE               | YES       |
| NHX-N-M          | HI TEMP CONNECTOR,ORANGE               | YES       |
| OST-J-F          | QUICK DISCONNECT T/C CONN,BLK          | YES       |
| OST-J-M          | QUICK DISCONNECT T/C CONN,BLK          | YES       |
| OST-K-F          | QUICK DISCONNECT T/C CONN,YEL.         | YES       |
| OST-K-M          | QUICK DISCONNECT T/C CONN,YEL.         | YES       |
| OST-N-F          | QUICK DISCONNECT T/C CONN,ORNG         | YES       |
| OST-N-M          | QUICK DISCONNECT T/C CONN,ORNG         | YES       |
| OST-R/S-F        | QUICK DISCONNECT T/C CONN,GRN          | YES       |
| OST-T-M          | QUICK DISCONNECT T/C CONN,BLUE         | YES       |
| OSTW-CC-K-125    | CAP CLAMP GROMMET 125OD 5/PK           | YES       |
| OSTW-CC-K-F      | INTEGRAL CABLE CLAMP CAP CONN          | YES       |
| OSTW-CC-K-M      | INTEGRAL CABLE CLAMP CAP CONN          | YES       |
| OSTW-CC-T-125    | CAP CLAMP GROMMET 125OD 5/PK           | YES       |
| OSTW-CC-T-M      | INTEGRAL CABLE CLAMP CAP CONN          | YES       |
| OSTW-C-F         | STD T/C CONN W/WINDOW,RED              | YES       |
| OSTW-C-M-S       | STD SOLID PIN CONNECTOR, RED           | YES       |
| OSTW-E-F         | STD T/C CONN W/WINDOW,PURPLE           | YES       |
| OSTW-E-M         | STD T/C CONN W/WINDOW,PURPLE           | YES       |
| OSTW-J-F         | STD T/C CONN W/WINDOW,BLACK            | YES       |
| OSTW-JJ-F-ROHS   | JIS T/C CONN W/WINDOW,YELLOW- MOQ 250  | YES       |
| OSTW-JJ-M-ROHS   | JIS T/C CONN W/WINDOW,YELLOW - MOQ 250 | YES       |
| OSTW-J-M         | STD T/C CONN W/WINDOW,BLACK            | YES       |
| OSTW-K-F         | STD T/C CONN W/WINDOW,YELLOW           | YES       |
| OSTW-KJ-F-ROHS   | JIS T/C CONN W/WINDOW,BLUE- MOQ 250    | YES       |
| OSTW-KJ-M-ROHS   | JIS T/C CONN W/WINDOW,BLUE- MOQ 250    | YES       |
| OSTW-K-M         | STD T/C CONN W/WINDOW,YELLOW           | YES       |
| OSTW-K-M-S       | STD SOLID PIN CONNECTOR,YELLOW         | YES       |
| OSTW-N-F         | STD T/C CONN W/WINDOW,ORANGE           | YES       |
| OSTW-N-M         | STD T/C CONN W/WINDOW,ORANGE           | YES       |
| OSTW-N-M-S       | STD SOLID PIN CONNECTOR,ORANGE         | YES       |
| OSTW-R/S-F       | STD T/C CONN W/WINDOW,GREEN            | YES       |
| OSTW-R/SJ-M-ROHS | JIS T/C CONN W/WINDOW,BLACK - MOQ 250  | YES       |
| OSTW-R/S-M       | STD T/C CONN W/WINDOW,GREEN            | YES       |
| OSTW-R/S-M-S     | STD SOLID PIN CONNECTOR, GREEN         | YES       |
| OSTW-T-F         | STD T/C CONN W/WINDOW,BLUE             | YES       |
| OSTW-TJ-F-ROHS   | STD T/C CONN W/WINDOW,BROWN- MOQ 250   | YES       |
| OSTW-TJ-M-ROHS   | JIS T/C CONN W/WINDOW,BROWN - MOQ 250  | YES       |
| OSTW-T-M         | STD T/C CONN W/WINDOW,BLUE             | YES       |
| OSTW-U-F         | STD T/C CONN W/WINDOW,WHITE            | YES       |
| OSTW-U-M         | STD T/C CONN W/WINDOW,WHITE            | YES       |
| OTP-E-F          | 3-PRONG T/C CONNECTOR,PURPLE           | YES       |
| OTP-E-M          | 3-PRONG T/C CONNECTOR,PURPLE           | YES       |
| OTP-J-F          | 3-PRONG T/C CONNECTOR,BLACK            | YES       |
| OTP-J-M          | 3-PRONG T/C CONNECTOR,BLACK            | YES       |
| OTP-K-F          | 3-PRONG T/C CONNECTOR,YELLOW           | YES       |
| OTP-K-M          | 3-PRONG T/C CONNECTOR,YELLOW           | YES       |
| OTP-N-F          | 3-PRONG T/C CONNECTOR,ORANGE           | YES       |
| OTP-N-M          | 3-PRONG T/C CONNECTOR,ORANGE           | YES       |
| OTP-T-F          | 3-PRONG T/C CONNECTOR,BLUE             | YES       |
| OTP-T-M          | 3-PRONG T/C CONNECTOR,BLUE             | YES       |
| OTP-U-F          | 3-PRONG T/C CONNECTOR,WHITE            | YES       |
| OTP-U-M          | 3-PRONG T/C CONNECTOR,WHITE            | YES       |
| PCLM             | CABLE CLAMP                            | YES       |
| PCLM-DTC         | CABLE CLAMP                            | YES       |
| PCLM-FT          | CABLE CLAMP                            | YES       |

| Item             | Description                     | Compliant |
|------------------|---------------------------------|-----------|
| PCLM-MTP         | CABLE CLAMP                     | YES       |
| PCLM-NHX         | CABLE CLAMP                     | YES       |
| PCLM-SHX         | CABLE CLAMP                     | YES       |
| PCLM-SMP         | CABLE CLAMP                     | YES       |
| PCLM-SMP-FT      | CABLE CLAMP                     | YES       |
| PCLM-SMP-RSC     | CABLE CLAMP                     | YES       |
| RB-SMP-100       | REDUCING BUSHING .100"ID 20/PK  | YES       |
| SA1-K            | SELF ADHESIVE T/C TYPE K 5/PK   | YES       |
| SB-OST-CR062-100 | CRIMPSTYLE SS BUSHING-100/PK    | YES       |
| SB-SMP-CR062-100 | CRIMPSTYLE SS BUSHING-100/PK    | YES       |
| SCPSS-020U-6     | SUB MINI T/C ASSEMBLY           | YES       |
| SFCL             | CONNECTOR SAFETY CLIP (10/PK)   | YES       |
| SHX-E-F          | SUB MINI HITEMP CONN,PURPLE     | YES       |
| SHX-J-F          | SUB MINI HI TEMP CONN,BLACK     | YES       |
| SHX-J-M          | SUB MINI HI TEMP CONN,BLACK     | YES       |
| SHX-K-F          | SUB MINI HITEMP CONN,YELLOW     | YES       |
| SHX-K-M          | SUB MINI HITEMP CONN,YELLOW     | YES       |
| SHX-N-M          | SUB MINI HITEMP CONN,ORANGE     | YES       |
| SHX-R/S-F        | SUB MINI HI TEMP CONN,GREEN     | YES       |
| SHX-R/S-M        | SUB MINI HI TEMP CONN,GREEN     | YES       |
| SL11-20          | SPADE LUG,ALLOY#11 (20/PK)      | YES       |
| SLAL-20          | SPADE LUG,ALOMEGA (20/PK)       | YES       |
| SLAL-20          | SPADE LUG,ALOMEGA (20/PK)       | YES       |
| SLCH-20          | SPADE LUG,CHROMEGA (20/PK)      | YES       |
| SLCH-20          | SPADE LUG,CHROMEGA (20/PK)      | YES       |
| SLCO-20          | SPADE LUG,CONSTANTAN (20/PK)    | YES       |
| SLCP-20          | SPADE LUG,COPPER (20/PK)        | YES       |
| SLIR-20          | SPADE LUG,IRON (20/PK)          | YES       |
| SLNN-20          | SPADE LUGS,NISIL (20/PK)        | YES       |
| SLNP-20          | SPADE LUGS,NICROSIL (20/PK)     | YES       |
| SM4-9-ROHS       | BACKSHELL 45/STRAIGHT(5 PER PK  | YES       |
| SM9-15-ROHS      | BACKSHELL 90/STRAIGHT-5 PK      | YES       |
| SMACL            | PANEL ADAPTOR CLIP              | YES       |
| SMCL             | SECURITY CLIP FOR SMPW 10/PK    | YES       |
| SM-CTHD          | HEAVY DUTY CRIMPING TOOL        | YES       |
| SMP-E-F          | SUB-MINI T/C CONNECTOR,PURPLE   | YES       |
| SMP-J-F          | SUB MINI T/C CONNECTOR,BLACK    | YES       |
| SMP-J-M          | SUB MINI T/C CONNECTOR,BLACK    | YES       |
| SMP-K-F          | SUB MINI T/C CONNECTOR,YELLOW   | YES       |
| SMP-K-M          | SUB MINI T/C CONNECTOR,YELLOW   | YES       |
| SMP-N-F          | SUB MINI T/C CONNECTOR,ORANGE   | YES       |
| SMP-N-M          | SUB MINI T/C CONNECTOR,ORANGE   | YES       |
| SMP-R/S-F        | SUB MINI T/C CONNECTOR,GREEN    | YES       |
| SMP-R/S-M        | SUB MINI T/C CONNECTOR,GREEN    | YES       |
| SMP-T-F          | SUB MINI T/C CONNECTOR,BLUE     | YES       |
| SMP-T-M          | SUB MINI T/C CONNECTOR,BLUE     | YES       |
| SMP-U-M          | SUB MINI T/C CONNECTOR,WHITE    | YES       |
| SMPW-CC-E-F      | CABLE CLAMP CAP SMPW CONNECTOR  | YES       |
| SMPW-CC-E-M      | CABLE CLAMP CAP SMPW CONNECTOR  | YES       |
| SMPW-CC-K-125    | CAP CLAMP GROMMET 125OD 5/PK    | YES       |
| SMPW-CC-K-F      | CABLE CLAMP CAP SMPW CONNECTOR  | YES       |
| SMPW-CC-K-M      | CABLE CLAMP CAP SMPW CONNECTOR  | YES       |
| SMPW-CC-R/S-M    | CABLE CLAMP CAP SMPW CONNECTOR  | YES       |
| SMPW-CC-T-125    | CAP CLAMP GROMMET 125OD 5/PK    | YES       |
| SMPW-CC-T-F      | CABLE CLAMP CAP SMPW CONNECTOR  | YES       |
| SMPW-CC-TI-125   | CAP CLAMP GROMMET 125OD 5/PK    | YES       |
| SMPW-CC-T-M      | CABLE CLAMP CAP SMPW CONNECTOR  | YES       |
| SMPW-E-M         | SUB-MINI CONN W/WINDOW,PURPLE   | YES       |
| SMPW-J-F         | SUB-MINI CONN W/WINDOW,BLACK    | YES       |
| SMPW-J-M         | SUB-MINI CONN W/WINDOW,BLACK    | YES       |
| SMPW-K-F         | SUB-MINI CONN W/WINDOW,YELLOW   | YES       |
| SMPW-KI-F        | IEC MINI CONN /WINDOW GREEN     | YES       |
| SMPW-KI-M        | IEC MINI CONN /WINDOW GREEN     | YES       |
| SMPW-KJ-F-ROHS   | JIS SUB-MINI CONN W/WINDOW,BLUE | YES       |

| Item              | Description                              | Compliant |
|-------------------|--|-----------|
| SMPW-KJ-M-ROHS    | JIS SUB-MINI CONN W/WINDOW,BLUE          | YES       |
| SMPW-K-M          | SUB-MINI CONN W/WINDOW,YELLOW            | YES       |
| SMPW-N-F          | SUB-MINI CONN W/WINDOW,ORANGE            | YES       |
| SMPW-N-M          | SUB-MINI CONN W/WINDOW,ORANGE            | YES       |
| SMPW-R/S-F        | SUB-MINI CONN W/WINDOW,GREEN             | YES       |
| SMPW-R/SJ-F-ROHS  | JIS SUB-MINI CONN W/WINDOW,BLACK         | YES       |
| SMPW-R/SJ-M-ROHS  | JIS SUB-MINI CONN W/WINDOW,BLACK         | YES       |
| SMPW-R/S-M        | SUB-MINI CONN W/WINDOW,GREEN             | YES       |
| SMPW-T-F          | SUB-MINI CONN W/WINDOW,BLUE              | YES       |
| SMPW-TJ-F-ROHS    | JIS SUB-MINI CONN W/WINDOW,BROWN         | YES       |
| SMPW-TJ-M-ROHS    | JIS SUB-MINI CONN W/WINDOW,BROWN         | YES       |
| SMPW-T-M          | SUB-MINI CONN W/WINDOW,BLUE              | YES       |
| SMPW-U-F          | SUB-MINI CONN W/WINDOW,WHITE             | YES       |
| SMPW-U-M          | SUB-MINI CONN W/WINDOW,WHITE             | YES       |
| SMTC-AL-P         | SUB MIN MALE PIN ALUMEL 100/PK           | YES       |
| SMTC-AL-S         | SUB MIN FEM.PIN ALUMEL 100/PK            | YES       |
| SMTC-BR-P         | SUB MINI MALE PIN BRASS 100/PK           | YES       |
| SMTC-CH-P         | SUB MIN MALE PIN CHROMEL 100PK           | YES       |
| SMTC-CH-S         | SUB MIN FEM.PIN CHROMEL 100/PK           | YES       |
| SMTC-CO-P         | SUB MIN MALE PIN CHROMEL 100PK           | YES       |
| SMTC-CO-S         | SUB MIN MALE PIN CHROMEL 100PK           | YES       |
| SMTC-CU-P         | SUB MIN MALE PIN CHROMEL 100PK           | YES       |
| SMTC-CU-S         | SUB MIN MALE PIN CHROMEL 100PK           | YES       |
| SMTC-IR-P         | SUB MIN MALE PIN CHROMEL 100PK           | YES       |
| SMTC-IR-S         | SUB MIN MALE PIN CHROMEL 100PK           | YES       |
| SMTC-ON-S         | SUB MIN MALE PIN CHROMEL 100PK           | YES       |
| SMTC-PBRZ-S       | SUB MINI MALE PIN BRASS 100/PK           | YES       |
| SPJ-E-F           | SNAP IN JACK CONNECTOR,PURPLE            | YES       |
| SPJ-J-F           | SNAP IN JACK CONNECTOR,BLACK             | YES       |
| SPJ-K-F           | SNAP IN JACK CONNECTOR,YELLOW            | YES       |
| SPJ-R/S-F         | SNAP IN JACK CONNECTOR,GREEN             | YES       |
| SPJ-T-F           | SNAP IN JACK CONNECTOR,BLUE              | YES       |
| SRB               | PROTECTIVE COVER FOR OST & OGP,BLACK     | YES       |
| SRBS              | OST HI-TEMP BOOT, GRAY                   | YES       |
| TFCC-005-500      | PFA COATED WIRE                          | YES       |
| TL11-20           | TERMINAL LUGS,ALLOY#11 (20/PK)           | YES       |
| TLAL-20           | TERMINAL LUGS,ALOMEGA(20/PK)             | YES       |
| TLCH-20           | TERMINAL LUGS,CHROMEGA (20/PK)           | YES       |
| TLCO-20           | TERMINAL LUGS,CONSTANTAN 20/PK           | YES       |
| TLCP-20           | TERMINAL LUGS,COPPER (20/PK)             | YES       |
| TLIR-20           | TERMINAL LUGS,IRON (20/PK)               | YES       |
| TLNN-20           | TERMINAL LUGS,NISIL (20/PK)              | YES       |
| TLNP-20           | TERMINAL LUGS,NICROSIL (20/PK)           | YES       |
| TPJ-E-F           | 3-PRONG T/C CONNECTOR                    | YES       |
| TPJ-J-F           | 3-PRONG T/C CONNECTOR                    | YES       |
| TPJ-K-F           | 3-PRONG T/C CONNECTOR                    | YES       |
| TPJ-T-F           | 3-PRONG T/C CONNECTOR                    | YES       |
| TPJ-U-F           | 3-PRONG T/C CONNECTOR                    | YES       |
| TT-K-24-TWSH-1000 | INSULATED T/C WIRE                       | YES       |
| TT-K-36-500       | INSULATED T/C WIRE                       | YES       |
| TT-T-36-500       | INSULATED T/C WIRE                       | YES       |
| XACL              | PANEL MOUNTING ADAPTOR CLIP              | YES       |
| XL-K-062-SLE-EM   | MINERAL INSULATED CABLE                  | YES       |
| XL-K-MO-062-CONT  | MINERAL INSULATED CABLE                  | YES       |
| XL-K-MO-062-SLE   | OMEGA CLAD XL W/ SPECIAL LIMITS OF ERROR | YES       |

※ " -ROHS " 無し品番でもROHS2の10物質に対応しております。