


白金抵抗測温体

検出器互換性公差図



RTD 温度 vs 抵抗値表

ヨーロッパ曲線、アルファ=0.00385、ITS-90

1°C単位で増加

| °C | Ω | 差 | °C | Ω | 差 | °C | Ω | 差 | °C | Ω | 差 | °C | Ω | 差 | °C | Ω | 差 |
|------|-------|------|------|-------|------|-----|-------|------|-----|-------|------|-----|--------|------|-----|--------|------|
| -200 | 18.52 | | -140 | 43.88 | 0.42 | -80 | 68.33 | 0.41 | -20 | 92.16 | 0.39 | ± 0 | 100.00 | 0.39 | +60 | 123.24 | 0.38 |
| 199 | 18.96 | 0.44 | 139 | 44.29 | 0.41 | 79 | 68.73 | 0.40 | 19 | 92.55 | 0.39 | + 1 | 100.39 | 0.39 | 61 | 123.62 | 0.38 |
| 198 | 19.39 | 0.43 | 138 | 44.71 | 0.42 | 78 | 69.13 | 0.40 | 18 | 92.95 | 0.40 | 2 | 100.78 | 0.39 | 62 | 124.01 | 0.39 |
| 197 | 19.82 | 0.43 | 137 | 45.12 | 0.41 | 77 | 69.53 | 0.40 | 17 | 93.34 | 0.39 | 3 | 101.17 | 0.39 | 63 | 124.39 | 0.38 |
| 196 | 20.25 | 0.43 | 136 | 45.53 | 0.41 | 76 | 69.93 | 0.40 | 16 | 93.73 | 0.39 | 4 | 101.56 | 0.39 | 64 | 124.77 | 0.38 |
| 195 | 20.68 | 0.43 | 135 | 45.95 | 0.42 | 75 | 70.33 | 0.40 | 15 | 94.12 | 0.39 | 5 | 101.95 | 0.39 | 65 | 125.17 | 0.40 |
| 194 | 21.11 | 0.43 | 134 | 46.35 | 0.40 | 74 | 70.73 | 0.40 | 14 | 94.52 | 0.40 | 6 | 102.34 | 0.39 | 66 | 125.55 | 0.38 |
| 193 | 21.54 | 0.43 | 133 | 46.76 | 0.41 | 73 | 71.13 | 0.40 | 13 | 94.91 | 0.39 | 7 | 102.73 | 0.39 | 67 | 125.93 | 0.38 |
| 192 | 21.97 | 0.43 | 132 | 47.18 | 0.42 | 72 | 71.53 | 0.40 | 12 | 95.30 | 0.39 | 8 | 103.12 | 0.39 | 68 | 126.32 | 0.39 |
| 191 | 22.40 | 0.43 | 131 | 47.59 | 0.41 | 71 | 71.93 | 0.40 | 11 | 95.69 | 0.39 | 9 | 103.51 | 0.39 | 69 | 126.70 | 0.38 |
| 190 | 22.83 | 0.43 | 130 | 48.00 | 0.41 | 70 | 72.33 | 0.40 | 10 | 96.09 | 0.40 | 10 | 103.90 | 0.39 | 70 | 127.08 | 0.38 |
| 189 | 23.26 | 0.43 | 129 | 48.41 | 0.41 | 69 | 72.73 | 0.40 | 9 | 96.48 | 0.39 | 11 | 104.29 | 0.39 | 71 | 127.46 | 0.38 |
| 188 | 23.69 | 0.43 | 128 | 48.82 | 0.41 | 68 | 73.13 | 0.40 | 8 | 96.87 | 0.39 | 12 | 104.68 | 0.39 | 72 | 127.85 | 0.39 |
| 187 | 24.12 | 0.43 | 127 | 49.23 | 0.41 | 67 | 73.53 | 0.40 | 7 | 97.26 | 0.39 | 13 | 105.07 | 0.39 | 73 | 128.23 | 0.38 |
| 186 | 24.55 | 0.43 | 126 | 49.64 | 0.41 | 66 | 73.93 | 0.40 | 6 | 97.65 | 0.39 | 14 | 105.46 | 0.39 | 74 | 128.61 | 0.38 |
| 185 | 24.97 | 0.42 | 125 | 50.06 | 0.42 | 65 | 74.33 | 0.40 | 5 | 98.04 | 0.39 | 15 | 105.85 | 0.39 | 75 | 128.99 | 0.38 |
| 184 | 25.39 | 0.42 | 124 | 50.47 | 0.41 | 64 | 74.73 | 0.40 | 4 | 98.44 | 0.40 | 16 | 106.24 | 0.39 | 76 | 129.38 | 0.39 |
| 183 | 25.82 | 0.43 | 123 | 50.88 | 0.41 | 63 | 75.13 | 0.40 | 3 | 98.83 | 0.39 | 17 | 106.63 | 0.39 | 77 | 129.76 | 0.38 |
| 182 | 26.25 | 0.43 | 122 | 51.29 | 0.41 | 62 | 75.53 | 0.40 | 2 | 99.22 | 0.39 | 18 | 107.02 | 0.39 | 78 | 130.14 | 0.38 |
| 181 | 26.67 | 0.42 | 121 | 51.70 | 0.41 | 61 | 75.93 | 0.40 | 1 | 99.61 | 0.39 | 19 | 107.40 | 0.38 | 79 | 130.52 | 0.38 |
| 180 | 27.10 | 0.43 | 120 | 52.11 | 0.41 | 60 | 76.33 | 0.40 | | | | 20 | 107.79 | 0.39 | 80 | 130.90 | 0.38 |
| 179 | 27.52 | 0.42 | 119 | 52.52 | 0.41 | 59 | 76.73 | 0.40 | | | | 21 | 108.18 | 0.39 | 81 | 131.28 | 0.38 |
| 178 | 27.95 | 0.43 | 118 | 52.92 | 0.40 | 58 | 77.13 | 0.40 | | | | 22 | 108.57 | 0.39 | 82 | 131.67 | 0.39 |
| 177 | 28.37 | 0.42 | 117 | 53.33 | 0.41 | 57 | 77.52 | 0.39 | | | | 23 | 108.96 | 0.39 | 83 | 132.05 | 0.38 |
| 176 | 28.80 | 0.43 | 116 | 53.74 | 0.41 | 56 | 77.92 | 0.40 | | | | 24 | 109.35 | 0.39 | 84 | 132.43 | 0.38 |
| 175 | 29.22 | 0.42 | 115 | 54.15 | 0.41 | 55 | 78.32 | 0.40 | | | | 25 | 109.73 | 0.38 | 85 | 132.81 | 0.38 |
| 174 | 29.65 | 0.43 | 114 | 54.56 | 0.41 | 54 | 78.72 | 0.40 | | | | 26 | 110.12 | 0.39 | 86 | 133.19 | 0.38 |
| 173 | 30.07 | 0.42 | 113 | 54.97 | 0.41 | 53 | 79.11 | 0.39 | | | | 27 | 110.51 | 0.39 | 87 | 133.57 | 0.38 |
| 172 | 30.49 | 0.42 | 112 | 55.38 | 0.41 | 52 | 79.51 | 0.40 | | | | 28 | 110.90 | 0.39 | 88 | 133.95 | 0.38 |
| 171 | 30.92 | 0.43 | 111 | 55.78 | 0.40 | 51 | 79.91 | 0.40 | | | | 29 | 111.28 | 0.38 | 89 | 134.33 | 0.38 |
| 170 | 31.34 | 0.42 | 110 | 56.19 | 0.41 | 50 | 80.31 | 0.40 | | | | 30 | 111.67 | 0.39 | 90 | 134.71 | 0.38 |
| 169 | 31.76 | 0.42 | 109 | 56.60 | 0.41 | 49 | 80.70 | 0.39 | | | | 31 | 112.06 | 0.39 | 91 | 135.09 | 0.38 |
| 168 | 32.18 | 0.42 | 108 | 57.00 | 0.40 | 48 | 81.10 | 0.40 | | | | 32 | 112.45 | 0.39 | 92 | 135.47 | 0.38 |
| 167 | 32.61 | 0.43 | 107 | 57.41 | 0.41 | 47 | 81.50 | 0.40 | | | | 33 | 112.83 | 0.38 | 93 | 135.85 | 0.38 |
| 166 | 33.03 | 0.42 | 106 | 57.82 | 0.41 | 46 | 81.89 | 0.39 | | | | 34 | 113.22 | 0.39 | 94 | 136.23 | 0.38 |
| 165 | 33.45 | 0.42 | 105 | 58.22 | 0.40 | 45 | 82.29 | 0.40 | | | | 35 | 113.61 | 0.39 | 95 | 136.61 | 0.38 |
| 164 | 33.86 | 0.41 | 104 | 58.63 | 0.41 | 44 | 82.69 | 0.40 | | | | 36 | 113.99 | 0.38 | 96 | 136.99 | 0.38 |
| 163 | 34.28 | 0.42 | 103 | 59.04 | 0.41 | 43 | 83.08 | 0.39 | | | | 37 | 114.38 | 0.39 | 97 | 137.37 | 0.38 |
| 162 | 34.70 | 0.42 | 102 | 59.44 | 0.40 | 42 | 83.48 | 0.40 | | | | 38 | 114.77 | 0.39 | 98 | 137.75 | 0.38 |
| 161 | 35.12 | 0.42 | 101 | 59.85 | 0.41 | 41 | 83.88 | 0.40 | | | | 39 | 115.15 | 0.38 | 99 | 138.13 | 0.38 |
| 160 | 35.54 | 0.42 | 100 | 60.26 | 0.41 | 40 | 84.27 | 0.39 | | | | 40 | 115.54 | 0.39 | 100 | 138.51 | 0.38 |
| 159 | 35.96 | 0.42 | 99 | 60.67 | 0.41 | 39 | 84.67 | 0.40 | | | | 41 | 115.93 | 0.39 | 101 | 138.89 | 0.38 |
| 158 | 36.38 | 0.42 | 98 | 61.07 | 0.40 | 38 | 85.06 | 0.39 | | | | 42 | 116.31 | 0.38 | 102 | 139.27 | 0.38 |
| 157 | 36.80 | 0.42 | 97 | 61.48 | 0.41 | 37 | 85.46 | 0.40 | | | | 43 | 116.70 | 0.39 | 103 | 139.65 | 0.38 |
| 156 | 37.22 | 0.42 | 96 | 61.87 | 0.41 | 36 | 85.85 | 0.39 | | | | 44 | 117.08 | 0.38 | 104 | 140.03 | 0.38 |
| 155 | 37.63 | 0.41 | 95 | 62.29 | 0.42 | 35 | 86.25 | 0.40 | | | | 45 | 117.47 | 0.39 | 105 | 140.39 | 0.36 |
| 154 | 38.05 | 0.42 | 94 | 62.69 | 0.40 | 34 | 86.64 | 0.39 | | | | 46 | 117.85 | 0.38 | 106 | 140.77 | 0.38 |
| 153 | 38.47 | 0.42 | 93 | 63.10 | 0.41 | 33 | 87.04 | 0.40 | | | | 47 | 118.24 | 0.39 | 107 | 141.15 | 0.38 |
| 152 | 38.89 | 0.42 | 92 | 63.50 | 0.40 | 32 | 87.43 | 0.39 | | | | 48 | 118.62 | 0.38 | 108 | 141.53 | 0.38 |
| 151 | 39.31 | 0.42 | 91 | 63.91 | 0.41 | 31 | 87.83 | 0.40 | | | | 49 | 119.01 | 0.39 | 109 | 141.91 | 0.38 |
| 150 | 39.72 | 0.41 | 90 | 64.30 | 0.39 | 30 | 88.22 | 0.39 | | | | 50 | 119.40 | 0.39 | 110 | 142.29 | 0.38 |
| 149 | 40.14 | 0.42 | 89 | 64.70 | 0.40 | 29 | 88.62 | 0.40 | | | | 51 | 119.78 | 0.38 | 111 | 142.66 | 0.37 |
| 148 | 40.56 | 0.42 | 88 | 65.11 | 0.41 | 28 | 89.01 | 0.39 | | | | 52 | 120.16 | 0.38 | 112 | 143.04 | 0.38 |
| 147 | 40.97 | 0.41 | 87 | 65.51 | 0.40 | 27 | 89.40 | 0.39 | | | | 53 | 120.55 | 0.39 | 113 | 143.42 | 0.38 |
| 146 | 41.39 | 0.42 | 86 | 65.91 | 0.40 | 26 | 89.80 | 0.40 | | | | 54 | 120.93 | 0.38 | 114 | 143.80 | 0.38 |
| 145 | 41.80 | 0.41 | 85 | 66.31 | 0.40 | 25 | 90.19 | 0.39 | | | | 55 | 121.32 | 0.39 | 115 | 144.18 | 0.38 |
| 144 | 42.22 | 0.42 | 84 | 66.72 | 0.41 | 24 | 90.59 | 0.40 | | | | 56 | 121.70 | 0.38 | 116 | 144.56 | 0.38 |
| 143 | 42.64 | 0.42 | 83 | 67.12 | 0.40 | 23 | 90.98 | 0.39 | | | | 57 | 122.09 | 0.39 | 117 | 144.94 | 0.38 |
| 142 | 43.05 | 0.41 | 82 | 67.52 | 0.40 | 22 | 91.37 | 0.39 | | | | 58 | 122.47 | 0.38 | 118 | 145.32 | 0.38 |
| 141 | 43.46 | 0.41 | 81 | 67.92 | 0.40 | 21 | 91.77 | 0.40 | | | | 59 | 122.86 | 0.39 | 119 | 145.69 | 0.37 |

注意: 100°Cでの抵抗値は138.50Ωです。

(DIN 43 760)

RTD 温度 vs 抵抗値表

ヨーロッパ曲線、アルファ=0.00385、ITS-90

1°C単位で増加

| °C | Ω | 差 |
|------|--------|------|------|--------|------|------|--------|------|------|--------|------|------|--------|------|------|--------|------|
| +120 | 146.07 | 0.38 | +180 | 168.48 | 0.37 | +240 | 190.47 | 0.36 | +300 | 212.05 | 0.36 | +360 | 233.21 | 0.35 | +420 | 253.96 | 0.34 |
| 121 | 146.45 | 0.38 | 181 | 168.85 | 0.37 | 241 | 190.83 | 0.36 | 301 | 212.40 | 0.35 | 361 | 233.56 | 0.35 | 421 | 254.30 | 0.34 |
| 122 | 146.82 | 0.37 | 182 | 169.22 | 0.37 | 242 | 191.20 | 0.37 | 302 | 212.76 | 0.36 | 362 | 233.91 | 0.35 | 422 | 254.65 | 0.35 |
| 123 | 147.20 | 0.38 | 183 | 169.59 | 0.37 | 243 | 191.56 | 0.36 | 303 | 213.12 | 0.36 | 363 | 234.26 | 0.35 | 423 | 254.99 | 0.34 |
| 124 | 147.58 | 0.38 | 184 | 169.96 | 0.37 | 244 | 191.92 | 0.36 | 304 | 213.47 | 0.35 | 364 | 234.60 | 0.36 | 424 | 255.33 | 0.34 |
| 125 | 147.95 | 0.37 | 185 | 170.33 | 0.37 | 245 | 192.28 | 0.36 | 305 | 213.83 | 0.36 | 365 | 234.95 | 0.35 | 425 | 255.67 | 0.34 |
| 126 | 148.33 | 0.38 | 186 | 170.69 | 0.36 | 246 | 192.66 | 0.38 | 306 | 214.19 | 0.36 | 366 | 235.30 | 0.35 | 426 | 256.01 | 0.34 |
| 127 | 148.71 | 0.38 | 187 | 171.06 | 0.37 | 247 | 193.02 | 0.36 | 307 | 214.55 | 0.36 | 367 | 235.65 | 0.35 | 427 | 256.35 | 0.34 |
| 128 | 149.08 | 0.37 | 188 | 171.43 | 0.37 | 248 | 193.38 | 0.36 | 308 | 214.90 | 0.35 | 368 | 236.00 | 0.35 | 428 | 256.70 | 0.35 |
| 129 | 149.46 | 0.38 | 189 | 171.80 | 0.37 | 249 | 193.74 | 0.36 | 309 | 215.26 | 0.36 | 369 | 236.35 | 0.35 | 429 | 257.04 | 0.34 |
| 130 | 149.83 | 0.37 | 190 | 172.17 | 0.37 | 250 | 194.10 | 0.36 | 310 | 215.61 | 0.35 | 370 | 236.70 | 0.35 | 430 | 257.38 | 0.34 |
| 131 | 150.21 | 0.38 | 191 | 172.54 | 0.37 | 251 | 194.47 | 0.37 | 311 | 215.97 | 0.36 | 371 | 237.05 | 0.35 | 431 | 257.72 | 0.34 |
| 132 | 150.58 | 0.37 | 192 | 172.91 | 0.37 | 252 | 194.83 | 0.36 | 312 | 216.32 | 0.35 | 372 | 237.40 | 0.35 | 432 | 258.06 | 0.34 |
| 133 | 150.96 | 0.38 | 193 | 173.27 | 0.36 | 253 | 195.19 | 0.36 | 313 | 216.68 | 0.36 | 373 | 237.75 | 0.35 | 433 | 258.40 | 0.34 |
| 134 | 151.34 | 0.38 | 194 | 173.64 | 0.37 | 254 | 195.55 | 0.36 | 314 | 217.03 | 0.35 | 374 | 238.09 | 0.34 | 434 | 258.74 | 0.34 |
| 135 | 151.71 | 0.37 | 195 | 174.01 | 0.37 | 255 | 195.90 | 0.35 | 315 | 217.39 | 0.36 | 375 | 238.44 | 0.35 | 435 | 259.08 | 0.34 |
| 136 | 152.09 | 0.38 | 196 | 174.39 | 0.38 | 256 | 196.26 | 0.36 | 316 | 217.73 | 0.34 | 376 | 238.79 | 0.35 | 436 | 259.42 | 0.34 |
| 137 | 152.46 | 0.37 | 197 | 174.75 | 0.36 | 257 | 196.62 | 0.36 | 317 | 218.08 | 0.35 | 377 | 239.14 | 0.35 | 437 | 259.76 | 0.34 |
| 138 | 152.84 | 0.38 | 198 | 175.12 | 0.37 | 258 | 196.98 | 0.36 | 318 | 218.44 | 0.36 | 378 | 239.48 | 0.34 | 438 | 260.10 | 0.34 |
| 139 | 153.21 | 0.37 | 199 | 175.49 | 0.37 | 259 | 197.35 | 0.37 | 319 | 218.79 | 0.35 | 379 | 239.83 | 0.35 | 439 | 260.44 | 0.34 |
| 140 | 153.58 | 0.37 | 200 | 175.86 | 0.37 | 260 | 197.71 | 0.36 | 320 | 219.15 | 0.36 | 380 | 240.18 | 0.35 | 440 | 260.78 | 0.34 |
| 141 | 153.95 | 0.37 | 201 | 176.23 | 0.37 | 261 | 198.07 | 0.36 | 321 | 219.50 | 0.35 | 381 | 240.52 | 0.34 | 441 | 261.12 | 0.34 |
| 142 | 154.32 | 0.37 | 202 | 176.59 | 0.36 | 262 | 198.43 | 0.36 | 322 | 219.85 | 0.35 | 382 | 240.87 | 0.35 | 442 | 261.46 | 0.34 |
| 143 | 154.71 | 0.39 | 203 | 176.96 | 0.37 | 263 | 198.79 | 0.36 | 323 | 220.21 | 0.36 | 383 | 241.22 | 0.35 | 443 | 261.80 | 0.34 |
| 144 | 155.08 | 0.37 | 204 | 177.33 | 0.37 | 264 | 199.15 | 0.36 | 324 | 220.56 | 0.35 | 384 | 241.56 | 0.34 | 444 | 262.14 | 0.34 |
| 145 | 155.46 | 0.38 | 205 | 177.70 | 0.37 | 265 | 199.51 | 0.36 | 325 | 220.91 | 0.35 | 385 | 241.91 | 0.35 | 445 | 262.48 | 0.34 |
| 146 | 155.83 | 0.37 | 206 | 178.06 | 0.36 | 266 | 199.87 | 0.36 | 326 | 221.27 | 0.36 | 386 | 242.25 | 0.34 | 446 | 262.83 | 0.35 |
| 147 | 156.21 | 0.38 | 207 | 178.43 | 0.37 | 267 | 200.23 | 0.36 | 327 | 221.62 | 0.35 | 387 | 242.60 | 0.35 | 447 | 263.17 | 0.34 |
| 148 | 156.58 | 0.37 | 208 | 178.80 | 0.37 | 268 | 200.59 | 0.36 | 328 | 221.97 | 0.35 | 388 | 242.95 | 0.35 | 448 | 263.50 | 0.33 |
| 149 | 156.96 | 0.38 | 209 | 179.16 | 0.36 | 269 | 200.95 | 0.36 | 329 | 222.32 | 0.35 | 389 | 243.29 | 0.34 | 449 | 263.84 | 0.34 |
| 150 | 157.33 | 0.37 | 210 | 179.53 | 0.37 | 270 | 201.31 | 0.36 | 330 | 222.68 | 0.36 | 390 | 243.64 | 0.35 | 450 | 264.18 | 0.34 |
| 151 | 157.71 | 0.38 | 211 | 179.90 | 0.37 | 271 | 201.67 | 0.36 | 331 | 223.03 | 0.35 | 391 | 243.98 | 0.34 | 451 | 264.52 | 0.34 |
| 152 | 158.08 | 0.37 | 212 | 180.26 | 0.36 | 272 | 202.03 | 0.36 | 332 | 223.38 | 0.35 | 392 | 244.33 | 0.35 | 452 | 264.86 | 0.34 |
| 153 | 158.45 | 0.37 | 213 | 180.63 | 0.37 | 273 | 202.38 | 0.35 | 333 | 223.73 | 0.35 | 393 | 244.67 | 0.34 | 453 | 265.20 | 0.34 |
| 154 | 158.83 | 0.38 | 214 | 180.99 | 0.36 | 274 | 202.74 | 0.36 | 334 | 224.09 | 0.36 | 394 | 245.02 | 0.35 | 454 | 265.54 | 0.34 |
| 155 | 159.20 | 0.37 | 215 | 181.36 | 0.37 | 275 | 203.10 | 0.36 | 335 | 224.45 | 0.36 | 395 | 245.36 | 0.34 | 455 | 265.87 | 0.33 |
| 156 | 159.56 | 0.36 | 216 | 181.73 | 0.37 | 276 | 203.46 | 0.36 | 336 | 224.80 | 0.35 | 396 | 245.71 | 0.35 | 456 | 266.21 | 0.34 |
| 157 | 159.94 | 0.38 | 217 | 182.09 | 0.36 | 277 | 203.82 | 0.36 | 337 | 225.15 | 0.35 | 397 | 246.05 | 0.34 | 457 | 266.55 | 0.34 |
| 158 | 160.31 | 0.37 | 218 | 182.46 | 0.37 | 278 | 204.18 | 0.36 | 338 | 225.50 | 0.35 | 398 | 246.40 | 0.35 | 458 | 266.89 | 0.34 |
| 159 | 160.68 | 0.37 | 219 | 182.82 | 0.36 | 279 | 204.54 | 0.36 | 339 | 225.85 | 0.35 | 399 | 246.74 | 0.34 | 459 | 267.22 | 0.33 |
| 160 | 161.05 | 0.37 | 220 | 183.19 | 0.37 | 280 | 204.90 | 0.36 | 340 | 226.21 | 0.36 | 400 | 247.09 | 0.35 | 460 | 267.56 | 0.34 |
| 161 | 161.43 | 0.38 | 221 | 183.55 | 0.36 | 281 | 205.25 | 0.35 | 341 | 226.56 | 0.35 | 401 | 247.43 | 0.34 | 461 | 267.90 | 0.34 |
| 162 | 161.80 | 0.37 | 222 | 183.92 | 0.37 | 282 | 205.61 | 0.36 | 342 | 226.91 | 0.35 | 402 | 247.78 | 0.35 | 462 | 268.24 | 0.34 |
| 163 | 162.17 | 0.37 | 223 | 184.28 | 0.36 | 283 | 205.97 | 0.36 | 343 | 227.26 | 0.35 | 403 | 248.12 | 0.34 | 463 | 268.57 | 0.33 |
| 164 | 162.54 | 0.37 | 224 | 184.65 | 0.37 | 284 | 206.33 | 0.36 | 344 | 227.61 | 0.35 | 404 | 248.46 | 0.34 | 464 | 268.91 | 0.34 |
| 165 | 162.91 | 0.37 | 225 | 185.01 | 0.36 | 285 | 206.70 | 0.37 | 345 | 227.96 | 0.35 | 405 | 248.81 | 0.35 | 465 | 269.25 | 0.34 |
| 166 | 163.28 | 0.37 | 226 | 185.38 | 0.37 | 286 | 207.05 | 0.35 | 346 | 228.31 | 0.35 | 406 | 249.15 | 0.34 | 466 | 269.58 | 0.33 |
| 167 | 163.66 | 0.38 | 227 | 185.74 | 0.36 | 287 | 207.41 | 0.36 | 347 | 228.66 | 0.35 | 407 | 249.50 | 0.35 | 467 | 269.92 | 0.34 |
| 168 | 164.03 | 0.37 | 228 | 186.11 | 0.37 | 288 | 207.77 | 0.36 | 348 | 229.01 | 0.35 | 408 | 249.84 | 0.34 | 468 | 270.26 | 0.34 |
| 169 | 164.40 | 0.37 | 229 | 186.47 | 0.36 | 289 | 208.13 | 0.36 | 349 | 229.36 | 0.35 | 409 | 250.18 | 0.34 | 469 | 270.59 | 0.33 |
| 170 | 164.77 | 0.37 | 230 | 186.84 | 0.37 | 290 | 208.48 | 0.35 | 350 | 229.72 | 0.34 | 410 | 250.53 | 0.35 | 470 | 270.93 | 0.34 |
| 171 | 165.14 | 0.37 | 231 | 187.20 | 0.36 | 291 | 208.84 | 0.36 | 351 | 230.07 | 0.35 | 411 | 250.89 | 0.34 | 471 | 271.27 | 0.34 |
| 172 | 165.51 | 0.37 | 232 | 187.56 | 0.36 | 292 | 209.20 | 0.36 | 352 | 230.42 | 0.35 | 412 | 251.21 | 0.34 | 472 | 271.60 | 0.33 |
| 173 | 165.88 | 0.37 | 233 | 187.93 | 0.37 | 293 | 209.55 | 0.35 | 353 | 230.77 | 0.35 | 413 | 251.55 | 0.34 | 473 | 271.94 | 0.34 |
| 174 | 166.25 | 0.37 | 234 | 188.29 | 0.36 | 294 | 209.91 | 0.36 | 354 | 231.12 | 0.35 | 414 | 251.90 | 0.35 | 474 | 272.27 | 0.33 |
| 175 | 166.62 | 0.37 | 235 | 188.65 | 0.36 | 295 | 210.27 | 0.36 | 355 | 231.47 | 0.35 | 415 | 252.24 | 0.34 | 475 | 272.61 | 0.34 |
| 176 | 167.00 | 0.38 | 236 | 189.02 | 0.37 | 296 | 210.62 | 0.35 | 356 | 231.81 | 0.36 | 416 | 252.59 | 0.35 | 476 | 272.95 | 0.34 |
| 177 | 167.37 | 0.37 | 237 | 189.38 | 0.36 | 297 | 210.98 | 0.36 | 357 | 232.16 | 0.35 | 417 | 252.94 | 0.35 | 477 | 273.28 | 0.33 |
| 178 | 167.74 | 0.37 | 238 | 189.74 | 0.36 | 298 | 211.34 | 0.36 | 358 | 232.51 | 0.35 | 418 | 253.28 | 0.34 | 478 | 273.62 | 0.34 |
| 179 | 168.11 | 0.37 | 239 | 190.11 | 0.37 | 299 | 211.69 | 0.35 | 359 | 232.86 | 0.35 | 419 | 253.62 | 0.34 | 479 | 273.95 | 0.33 |

注意: 100°Cでの抵抗値は138.50Ωです。

(DIN 43 760)

RTD 温度 vs 抵抗値表

ヨーロッパ曲線、アルファ=0.00385、ITS-90

1°C単位で増加

| °C | Ω | 差 |
|------|--------|------|------|--------|------|------|--------|------|------|--------|------|------|--------|------|------|--------|------|
| +480 | 274.29 | 0.34 | +542 | 294.87 | 0.33 | +604 | 315.00 | 0.32 | +666 | 334.68 | 0.32 | +728 | 353.91 | 0.30 | +790 | 372.71 | 0.30 |
| 481 | 274.62 | 0.33 | 543 | 295.20 | 0.33 | 605 | 315.32 | 0.32 | 667 | 334.99 | 0.31 | 729 | 354.22 | 0.31 | 791 | 373.01 | 0.30 |
| 482 | 274.96 | 0.34 | 544 | 295.53 | 0.33 | 606 | 315.64 | 0.32 | 668 | 335.31 | 0.32 | 730 | 354.53 | 0.31 | 792 | 373.31 | 0.30 |
| 483 | 275.29 | 0.33 | 545 | 295.85 | 0.32 | 607 | 315.96 | 0.32 | 669 | 335.62 | 0.31 | 731 | 354.83 | 0.30 | 793 | 373.61 | 0.30 |
| 484 | 275.63 | 0.34 | 546 | 296.18 | 0.33 | 608 | 316.28 | 0.32 | 670 | 335.93 | 0.31 | 732 | 355.14 | 0.31 | 794 | 373.91 | 0.30 |
| 485 | 275.96 | 0.33 | 547 | 296.51 | 0.33 | 609 | 316.60 | 0.32 | 671 | 336.25 | 0.32 | 733 | 355.44 | 0.30 | 795 | 374.21 | 0.30 |
| 486 | 276.31 | 0.34 | 548 | 296.84 | 0.33 | 610 | 316.92 | 0.32 | 672 | 336.56 | 0.31 | 734 | 355.75 | 0.31 | 796 | 374.51 | 0.30 |
| 487 | 276.64 | 0.33 | 549 | 297.16 | 0.32 | 611 | 317.24 | 0.32 | 673 | 336.87 | 0.31 | 735 | 356.06 | 0.31 | 797 | 374.80 | 0.29 |
| 488 | 276.97 | 0.33 | 550 | 297.49 | 0.33 | 612 | 317.56 | 0.32 | 674 | 337.18 | 0.31 | 736 | 356.37 | 0.31 | 798 | 374.10 | 0.30 |
| 489 | 277.31 | 0.34 | 551 | 297.82 | 0.33 | 613 | 317.88 | 0.32 | 675 | 337.50 | 0.32 | 737 | 356.68 | 0.31 | 799 | 375.40 | 0.30 |
| 490 | 277.64 | 0.33 | 552 | 298.14 | 0.32 | 614 | 318.20 | 0.32 | 676 | 337.81 | 0.31 | 738 | 356.98 | 0.30 | 800 | 375.70 | 0.30 |
| 491 | 277.98 | 0.34 | 553 | 298.47 | 0.33 | 615 | 318.52 | 0.32 | 677 | 338.12 | 0.31 | 739 | 357.29 | 0.31 | 801 | 376.00 | 0.30 |
| 492 | 278.31 | 0.33 | 554 | 298.80 | 0.33 | 616 | 318.85 | 0.33 | 678 | 338.43 | 0.31 | 740 | 357.59 | 0.30 | 802 | 376.29 | 0.29 |
| 493 | 278.64 | 0.33 | 555 | 299.12 | 0.32 | 617 | 319.17 | 0.32 | 679 | 338.75 | 0.32 | 741 | 357.90 | 0.31 | 803 | 376.59 | 0.30 |
| 494 | 278.98 | 0.34 | 556 | 299.45 | 0.33 | 618 | 319.49 | 0.32 | 680 | 339.06 | 0.31 | 742 | 358.20 | 0.30 | 804 | 376.89 | 0.30 |
| 495 | 279.31 | 0.33 | 557 | 299.78 | 0.33 | 619 | 319.81 | 0.32 | 681 | 339.37 | 0.31 | 743 | 358.51 | 0.31 | 805 | 377.19 | 0.30 |
| 496 | 279.64 | 0.33 | 558 | 300.10 | 0.32 | 620 | 320.12 | 0.31 | 682 | 339.68 | 0.31 | 744 | 358.81 | 0.30 | 806 | 377.49 | 0.30 |
| 497 | 279.98 | 0.34 | 559 | 300.43 | 0.33 | 621 | 320.44 | 0.32 | 683 | 339.99 | 0.31 | 745 | 359.12 | 0.31 | 807 | 377.79 | 0.30 |
| 498 | 280.31 | 0.33 | 560 | 300.75 | 0.32 | 622 | 320.76 | 0.32 | 684 | 340.30 | 0.31 | 746 | 359.42 | 0.30 | 808 | 378.09 | 0.30 |
| 499 | 280.64 | 0.33 | 561 | 301.08 | 0.33 | 623 | 321.08 | 0.32 | 685 | 340.62 | 0.32 | 747 | 359.72 | 0.30 | 809 | 378.39 | 0.30 |
| 500 | 280.98 | 0.34 | 562 | 301.41 | 0.33 | 624 | 321.40 | 0.32 | 686 | 340.94 | 0.32 | 748 | 360.03 | 0.31 | 810 | 378.68 | 0.29 |
| 501 | 281.31 | 0.33 | 563 | 301.73 | 0.32 | 625 | 321.72 | 0.32 | 687 | 341.25 | 0.31 | 749 | 360.33 | 0.30 | 811 | 378.98 | 0.30 |
| 502 | 281.64 | 0.33 | 564 | 302.06 | 0.33 | 626 | 322.03 | 0.31 | 688 | 341.55 | 0.30 | 750 | 360.64 | 0.31 | 812 | 379.28 | 0.30 |
| 503 | 281.97 | 0.33 | 565 | 302.38 | 0.32 | 627 | 322.34 | 0.31 | 689 | 341.87 | 0.32 | 751 | 360.94 | 0.30 | 813 | 379.57 | 0.29 |
| 504 | 282.31 | 0.34 | 566 | 302.71 | 0.33 | 628 | 322.66 | 0.32 | 690 | 342.18 | 0.31 | 752 | 361.24 | 0.30 | 814 | 379.87 | 0.30 |
| 505 | 282.64 | 0.33 | 567 | 303.03 | 0.32 | 629 | 322.98 | 0.32 | 691 | 342.49 | 0.31 | 753 | 361.55 | 0.31 | 815 | 380.17 | 0.30 |
| 506 | 282.97 | 0.33 | 568 | 303.36 | 0.33 | 630 | 323.30 | 0.32 | 692 | 342.80 | 0.31 | 754 | 361.85 | 0.30 | 816 | 380.46 | 0.29 |
| 507 | 283.30 | 0.33 | 569 | 303.68 | 0.32 | 631 | 323.61 | 0.31 | 693 | 343.11 | 0.31 | 755 | 362.15 | 0.30 | 817 | 380.76 | 0.30 |
| 508 | 283.63 | 0.33 | 570 | 304.01 | 0.33 | 632 | 323.93 | 0.32 | 694 | 343.42 | 0.31 | 756 | 362.46 | 0.31 | 818 | 381.05 | 0.29 |
| 509 | 283.97 | 0.34 | 571 | 304.33 | 0.32 | 633 | 324.25 | 0.32 | 695 | 343.73 | 0.31 | 757 | 362.76 | 0.30 | 819 | 381.35 | 0.30 |
| 510 | 284.30 | 0.33 | 572 | 304.66 | 0.33 | 634 | 324.57 | 0.32 | 696 | 344.04 | 0.31 | 758 | 363.06 | 0.30 | 820 | 381.65 | 0.30 |
| 511 | 284.63 | 0.33 | 573 | 304.98 | 0.32 | 635 | 324.88 | 0.31 | 697 | 344.35 | 0.31 | 759 | 363.36 | 0.30 | 821 | 381.94 | 0.29 |
| 512 | 284.96 | 0.33 | 574 | 305.30 | 0.32 | 636 | 325.21 | 0.33 | 698 | 344.66 | 0.31 | 760 | 363.67 | 0.31 | 822 | 382.24 | 0.30 |
| 513 | 285.29 | 0.33 | 575 | 305.63 | 0.33 | 637 | 325.53 | 0.32 | 699 | 344.97 | 0.31 | 761 | 363.97 | 0.30 | 823 | 382.53 | 0.29 |
| 514 | 285.62 | 0.33 | 576 | 305.95 | 0.32 | 638 | 325.85 | 0.32 | 700 | 345.28 | 0.31 | 762 | 364.27 | 0.30 | 824 | 382.83 | 0.30 |
| 515 | 285.95 | 0.33 | 577 | 306.28 | 0.33 | 639 | 326.16 | 0.31 | 701 | 345.59 | 0.31 | 763 | 364.57 | 0.30 | 825 | 383.12 | 0.29 |
| 516 | 286.30 | 0.35 | 578 | 306.60 | 0.32 | 640 | 326.48 | 0.32 | 702 | 345.90 | 0.31 | 764 | 364.88 | 0.31 | 826 | 383.42 | 0.30 |
| 517 | 286.63 | 0.33 | 579 | 306.92 | 0.32 | 641 | 326.79 | 0.31 | 703 | 346.21 | 0.31 | 765 | 365.18 | 0.30 | 827 | 383.71 | 0.29 |
| 518 | 286.96 | 0.33 | 580 | 307.25 | 0.33 | 642 | 327.11 | 0.32 | 704 | 346.52 | 0.31 | 766 | 365.49 | 0.31 | 828 | 384.01 | 0.30 |
| 519 | 287.29 | 0.33 | 581 | 307.57 | 0.32 | 643 | 327.43 | 0.32 | 705 | 346.83 | 0.31 | 767 | 365.79 | 0.30 | 829 | 384.30 | 0.29 |
| 520 | 287.62 | 0.33 | 582 | 307.89 | 0.32 | 644 | 327.74 | 0.31 | 706 | 346.15 | 0.32 | 768 | 366.09 | 0.30 | 830 | 384.60 | 0.30 |
| 521 | 287.95 | 0.33 | 583 | 308.22 | 0.33 | 645 | 328.06 | 0.32 | 707 | 347.46 | 0.31 | 769 | 366.40 | 0.31 | 831 | 384.89 | 0.29 |
| 522 | 288.28 | 0.33 | 584 | 308.54 | 0.32 | 646 | 328.38 | 0.32 | 708 | 347.76 | 0.30 | 770 | 366.70 | 0.30 | 832 | 385.18 | 0.29 |
| 523 | 288.61 | 0.33 | 585 | 308.86 | 0.32 | 647 | 328.69 | 0.31 | 709 | 348.07 | 0.31 | 771 | 367.00 | 0.30 | 833 | 385.48 | 0.30 |
| 524 | 288.94 | 0.33 | 586 | 309.19 | 0.33 | 648 | 329.01 | 0.32 | 710 | 348.38 | 0.31 | 772 | 367.30 | 0.30 | 834 | 385.77 | 0.29 |
| 525 | 289.27 | 0.33 | 587 | 309.51 | 0.32 | 649 | 329.32 | 0.31 | 711 | 348.69 | 0.31 | 773 | 367.60 | 0.30 | 835 | 386.07 | 0.30 |
| 526 | 289.60 | 0.33 | 588 | 309.83 | 0.32 | 650 | 329.64 | 0.32 | 712 | 349.00 | 0.31 | 774 | 367.90 | 0.30 | 836 | 386.37 | 0.30 |
| 527 | 289.93 | 0.33 | 589 | 310.15 | 0.32 | 651 | 329.95 | 0.31 | 713 | 349.31 | 0.31 | 775 | 368.20 | 0.30 | 837 | 386.66 | 0.29 |
| 528 | 290.26 | 0.33 | 590 | 310.48 | 0.33 | 652 | 330.27 | 0.32 | 714 | 349.61 | 0.30 | 776 | 368.50 | 0.30 | 838 | 386.96 | 0.30 |
| 529 | 290.59 | 0.33 | 591 | 310.80 | 0.32 | 653 | 330.58 | 0.31 | 715 | 349.92 | 0.31 | 777 | 368.81 | 0.31 | 839 | 387.25 | 0.29 |
| 530 | 290.92 | 0.33 | 592 | 311.12 | 0.32 | 654 | 330.90 | 0.32 | 716 | 350.23 | 0.31 | 778 | 369.11 | 0.30 | 840 | 387.55 | 0.30 |
| 531 | 291.25 | 0.33 | 593 | 311.45 | 0.33 | 655 | 331.21 | 0.31 | 717 | 350.54 | 0.31 | 779 | 369.41 | 0.30 | 841 | 387.84 | 0.29 |
| 532 | 291.58 | 0.33 | 594 | 311.78 | 0.33 | 656 | 331.53 | 0.32 | 718 | 350.85 | 0.31 | 780 | 369.71 | 0.30 | 842 | 388.13 | 0.29 |
| 533 | 291.90 | 0.32 | 595 | 312.10 | 0.32 | 657 | 331.84 | 0.31 | 719 | 351.15 | 0.30 | 781 | 370.01 | 0.30 | 843 | 388.42 | 0.29 |
| 534 | 292.23 | 0.33 | 596 | 312.43 | 0.33 | 658 | 332.16 | 0.32 | 720 | 351.46 | 0.31 | 782 | 370.31 | 0.30 | 844 | 388.72 | 0.30 |
| 535 | 292.56 | 0.33 | 597 | 312.75 | 0.32 | 659 | 332.47 | 0.31 | 721 | 351.77 | 0.31 | 783 | 370.61 | 0.30 | 845 | 389.01 | 0.29 |
| 536 | 292.90 | 0.34 | 598 | 313.07 | 0.32 | 660 | 332.79 | 0.32 | 722 | 352.07 | 0.30 | 784 | 370.91 | 0.30 | 846 | 389.31 | 0.30 |
| 537 | 293.23 | 0.33 | 599 | 313.39 | 0.32 | 661 | 333.10 | 0.31 | 723 | 352.38 | 0.31 | 785 | 371.21 | 0.30 | 847 | 389.61 | 0.30 |
| 538 | 293.56 | 0.33 | 600 | 313.71 | 0.32 | 662 | 333.41 | 0.31 | 724 | 352.69 | 0.31 | 786 | 371.52 | 0.31 | 848 | 389.90 | 0.29 |
| 539 | 293.89 | 0.33 | 601 | 314.04 | 0.33 | 663 | 333.73 | 0.32 | 725 | 352.99 | 0.30 | 787 | 371.82 | 0.30 | 849 | 390.19 | 0.29 |
| 540 | 294.21 | 0.32 | 602 | 314.36 | 0.32 | 664 | 334.04 | 0.31 | 726 | 353.30 | 0.31 | 788 | 372.12 | 0.30 | 850 | 390.48 | 0.29 |
| 541 | 294.54 | 0.33 | 603 | 314.68 | 0.32 | 665 | 334.36 | 0.32 | 727 | 353.61 | 0.31 | 789 | 372.41 | 0.29 | | | |

注意: 100°Cでの抵抗値は138.50Ωです。

温度-232

(DIN 43 760)

RTD 温度 vs 抵抗値表

アメリカ曲線、アルファ=0.00392

1°C単位で増加

| ° C | Ω | ° C | Ω | ° C | Ω | ° C | Ω | ° C | Ω | ° C | Ω | ° C | Ω | ° C | Ω | ° C | Ω |
|------|-------|-----|--------|-----|--------|-----|--------|-----|--------|-----|--------|-----|--------|-----|--------|-----|--------|
| -100 | 59.57 | -38 | 84.80 | 24 | 109.51 | 86 | 133.75 | 148 | 157.53 | 210 | 180.86 | 272 | 203.74 | 334 | 226.17 | 396 | 248.16 |
| -99 | 59.98 | -37 | 85.20 | 25 | 109.90 | 87 | 134.14 | 149 | 157.91 | 211 | 181.23 | 273 | 204.11 | 335 | 226.53 | 397 | 248.51 |
| -98 | 60.39 | -36 | 85.60 | 26 | 110.30 | 88 | 134.52 | 150 | 158.29 | 212 | 181.61 | 274 | 204.47 | 336 | 226.89 | 398 | 248.86 |
| -97 | 60.80 | -35 | 86.01 | 27 | 110.69 | 89 | 134.91 | 151 | 158.67 | 213 | 181.98 | 275 | 204.84 | 337 | 227.25 | 399 | 249.21 |
| -96 | 61.21 | -34 | 86.41 | 28 | 111.09 | 90 | 135.30 | 152 | 159.05 | 214 | 182.35 | 276 | 205.20 | 338 | 227.61 | 400 | 249.56 |
| -95 | 61.63 | -33 | 86.81 | 29 | 111.48 | 91 | 135.68 | 153 | 159.43 | 215 | 182.72 | 277 | 205.57 | 339 | 227.96 | 401 | 249.91 |
| -94 | 62.04 | -32 | 87.21 | 30 | 111.88 | 92 | 136.07 | 154 | 159.81 | 216 | 183.09 | 278 | 205.93 | 340 | 228.32 | 402 | 250.26 |
| -93 | 62.45 | -31 | 87.61 | 31 | 112.27 | 93 | 136.46 | 155 | 160.19 | 217 | 183.47 | 279 | 206.30 | 341 | 228.68 | 403 | 250.61 |
| -92 | 62.86 | -30 | 88.01 | 32 | 112.66 | 94 | 136.84 | 156 | 160.57 | 218 | 183.84 | 280 | 206.66 | 342 | 229.04 | 404 | 250.96 |
| -91 | 63.27 | -29 | 88.42 | 33 | 113.06 | 95 | 137.23 | 157 | 160.95 | 219 | 184.21 | 281 | 207.02 | 343 | 229.39 | 405 | 251.31 |
| -90 | 63.68 | -28 | 88.82 | 34 | 113.45 | 96 | 137.62 | 158 | 161.33 | 220 | 184.58 | 282 | 207.39 | 344 | 229.75 | 406 | 251.66 |
| -89 | 64.09 | -27 | 89.22 | 35 | 113.84 | 97 | 138.00 | 159 | 161.70 | 221 | 184.95 | 283 | 207.75 | 345 | 230.11 | 407 | 252.01 |
| -88 | 64.50 | -26 | 89.62 | 36 | 114.24 | 98 | 138.39 | 160 | 162.08 | 222 | 185.32 | 284 | 208.12 | 346 | 230.46 | 408 | 252.36 |
| -87 | 64.91 | -25 | 90.02 | 37 | 114.63 | 99 | 138.77 | 161 | 162.46 | 223 | 185.70 | 285 | 208.48 | 347 | 230.82 | 409 | 252.71 |
| -86 | 65.32 | -24 | 90.42 | 38 | 115.02 | 100 | 139.16 | 162 | 162.84 | 224 | 186.07 | 286 | 208.85 | 348 | 231.18 | 410 | 253.06 |
| -85 | 65.73 | -23 | 90.82 | 39 | 115.42 | 101 | 139.55 | 163 | 163.22 | 225 | 186.44 | 287 | 209.21 | 349 | 231.53 | 411 | 253.41 |
| -84 | 66.14 | -22 | 91.22 | 40 | 115.81 | 102 | 139.93 | 164 | 163.60 | 226 | 186.81 | 288 | 209.57 | 350 | 231.89 | 412 | 253.76 |
| -83 | 66.55 | -21 | 91.62 | 41 | 116.20 | 103 | 140.32 | 165 | 163.97 | 227 | 187.18 | 289 | 209.94 | 351 | 232.25 | 413 | 254.11 |
| -82 | 66.96 | -20 | 92.02 | 42 | 116.59 | 104 | 140.70 | 166 | 164.35 | 228 | 187.55 | 290 | 210.30 | 352 | 232.60 | 414 | 254.46 |
| -81 | 67.36 | -19 | 92.42 | 43 | 116.99 | 105 | 141.09 | 167 | 164.73 | 229 | 187.92 | 291 | 210.66 | 353 | 232.96 | 415 | 254.80 |
| -80 | 67.77 | -18 | 92.82 | 44 | 117.38 | 106 | 141.47 | 168 | 165.11 | 230 | 188.29 | 292 | 211.03 | 354 | 233.31 | 416 | 255.15 |
| -79 | 68.18 | -17 | 93.22 | 45 | 117.77 | 107 | 141.86 | 169 | 165.48 | 231 | 188.66 | 293 | 211.39 | 355 | 233.67 | 417 | 255.50 |
| -78 | 68.59 | -16 | 93.62 | 46 | 118.16 | 108 | 142.24 | 170 | 165.86 | 232 | 189.03 | 294 | 211.75 | 356 | 234.03 | 418 | 255.85 |
| -77 | 69.00 | -15 | 94.02 | 47 | 118.56 | 109 | 142.63 | 171 | 166.24 | 233 | 189.40 | 295 | 212.11 | 357 | 234.38 | 419 | 256.20 |
| -76 | 69.41 | -14 | 94.42 | 48 | 118.95 | 110 | 143.01 | 172 | 166.62 | 234 | 189.77 | 296 | 212.48 | 358 | 234.74 | 420 | 256.55 |
| -75 | 69.81 | -13 | 94.82 | 49 | 119.34 | 111 | 143.39 | 173 | 166.99 | 235 | 190.14 | 297 | 212.84 | 359 | 235.09 | 421 | 256.89 |
| -74 | 70.22 | -12 | 95.22 | 50 | 119.73 | 112 | 143.78 | 174 | 167.37 | 236 | 190.51 | 298 | 213.20 | 360 | 235.45 | 422 | 257.24 |
| -73 | 70.63 | -11 | 95.62 | 51 | 120.12 | 113 | 144.16 | 175 | 167.75 | 237 | 190.88 | 299 | 213.56 | 361 | 235.80 | 423 | 257.59 |
| -72 | 71.04 | -10 | 96.02 | 52 | 120.51 | 114 | 144.55 | 176 | 168.12 | 238 | 191.25 | 300 | 213.93 | 362 | 236.16 | 424 | 257.94 |
| -71 | 71.44 | -9 | 96.42 | 53 | 120.91 | 115 | 144.93 | 177 | 168.50 | 239 | 191.62 | 301 | 214.29 | 363 | 236.51 | 425 | 258.29 |
| -70 | 71.85 | -8 | 96.81 | 54 | 121.30 | 116 | 145.31 | 178 | 168.88 | 240 | 191.99 | 302 | 214.65 | 364 | 236.87 | 426 | 258.63 |
| -69 | 72.26 | -7 | 97.21 | 55 | 121.69 | 117 | 145.70 | 179 | 169.25 | 241 | 192.36 | 303 | 215.01 | 365 | 237.22 | 427 | 258.98 |
| -68 | 72.66 | -6 | 97.61 | 56 | 122.08 | 118 | 146.08 | 180 | 169.63 | 242 | 192.73 | 304 | 215.37 | 366 | 237.58 | 428 | 259.33 |
| -67 | 73.07 | -5 | 98.01 | 57 | 122.47 | 119 | 146.47 | 181 | 170.00 | 243 | 193.09 | 305 | 215.74 | 367 | 237.93 | 429 | 259.67 |
| -66 | 73.48 | -4 | 98.41 | 58 | 122.86 | 120 | 146.85 | 182 | 170.38 | 244 | 193.46 | 306 | 216.10 | 368 | 238.28 | 430 | 260.02 |
| -65 | 73.88 | -3 | 98.81 | 59 | 123.25 | 121 | 147.23 | 183 | 170.76 | 245 | 193.83 | 307 | 216.46 | 369 | 238.64 | 431 | 260.37 |
| -64 | 74.29 | -2 | 99.20 | 60 | 123.64 | 122 | 147.61 | 184 | 171.13 | 246 | 194.20 | 308 | 216.82 | 370 | 238.99 | 432 | 260.72 |
| -63 | 74.70 | -1 | 99.60 | 61 | 124.03 | 123 | 148.00 | 185 | 171.51 | 247 | 194.57 | 309 | 217.18 | 371 | 239.35 | 433 | 261.06 |
| -62 | 75.10 | 0 | 100.00 | 62 | 124.42 | 124 | 148.38 | 186 | 171.88 | 248 | 194.94 | 310 | 217.54 | 372 | 239.70 | 434 | 261.41 |
| -61 | 75.51 | 1 | 100.40 | 63 | 124.81 | 125 | 148.76 | 187 | 172.26 | 249 | 195.31 | 311 | 217.90 | 373 | 240.05 | 435 | 261.75 |
| -60 | 75.91 | 2 | 100.80 | 64 | 125.20 | 126 | 149.15 | 188 | 172.63 | 250 | 195.67 | 312 | 218.26 | 374 | 240.41 | 436 | 262.10 |
| -59 | 76.32 | 3 | 101.19 | 65 | 125.59 | 127 | 149.53 | 189 | 173.01 | 251 | 196.04 | 313 | 218.63 | 375 | 240.76 | 437 | 262.45 |
| -58 | 76.72 | 4 | 101.59 | 66 | 125.98 | 128 | 149.91 | 190 | 173.38 | 252 | 196.41 | 314 | 218.99 | 376 | 241.11 | 438 | 262.79 |
| -57 | 77.13 | 5 | 101.99 | 67 | 126.37 | 129 | 150.29 | 191 | 173.76 | 253 | 196.78 | 315 | 219.35 | 377 | 241.47 | 439 | 263.14 |
| -56 | 77.53 | 6 | 102.38 | 68 | 126.76 | 130 | 150.67 | 192 | 174.13 | 254 | 197.14 | 316 | 219.71 | 378 | 241.82 | 440 | 263.49 |
| -55 | 77.94 | 7 | 102.78 | 69 | 127.15 | 131 | 151.06 | 193 | 174.51 | 255 | 197.51 | 317 | 220.07 | 379 | 242.17 | 441 | 263.83 |
| -54 | 78.34 | 8 | 103.18 | 70 | 127.54 | 132 | 151.44 | 194 | 174.88 | 256 | 197.88 | 318 | 220.43 | 380 | 242.53 | 442 | 264.18 |
| -53 | 78.75 | 9 | 103.57 | 71 | 127.93 | 133 | 151.82 | 195 | 175.26 | 257 | 198.25 | 319 | 220.79 | 381 | 242.88 | 443 | 264.52 |
| -52 | 79.15 | 10 | 103.97 | 72 | 128.32 | 134 | 152.20 | 196 | 175.63 | 258 | 198.61 | 320 | 221.15 | 382 | 243.23 | 444 | 264.87 |
| -51 | 79.56 | 11 | 104.37 | 73 | 128.71 | 135 | 152.58 | 197 | 176.01 | 259 | 198.98 | 321 | 221.51 | 383 | 243.58 | 445 | 265.21 |
| -50 | 79.96 | 12 | 104.76 | 74 | 129.09 | 136 | 152.96 | 198 | 176.38 | 260 | 199.35 | 322 | 221.87 | 384 | 243.94 | 446 | 265.56 |
| -49 | 80.36 | 13 | 105.16 | 75 | 129.48 | 137 | 153.35 | 199 | 176.75 | 261 | 199.71 | 323 | 222.23 | 385 | 244.29 | 447 | 265.90 |
| -48 | 80.77 | 14 | 105.56 | 76 | 129.87 | 138 | 153.73 | 200 | 177.13 | 262 | 200.08 | 324 | 222.59 | 386 | 244.64 | 448 | 266.25 |
| -47 | 81.17 | 15 | 105.95 | 77 | 130.26 | 139 | 154.11 | 201 | 177.50 | 263 | 200.45 | 325 | 222.94 | 387 | 244.99 | 449 | 266.59 |
| -46 | 81.58 | 16 | 106.35 | 78 | 130.65 | 140 | 154.49 | 202 | 177.88 | 264 | 200.81 | 326 | 223.30 | 388 | 245.35 | 450 | 266.94 |
| -45 | 81.98 | 17 | 106.74 | 79 | 131.04 | 141 | 154.87 | 203 | 178.25 | 265 | 201.18 | 327 | 223.66 | 389 | 245.70 | 451 | 267.28 |
| -44 | 82.38 | 18 | 107.14 | 80 | 131.42 | 142 | 155.25 | 204 | 178.62 | 266 | 201.55 | 328 | 224.02 | 390 | 246.05 | 452 | 267.63 |
| -43 | 82.79 | 19 | 107.53 | 81 | 131.81 | 143 | 155.63 | 205 | 179.00 | 267 | 201.91 | 329 | 224.38 | 391 | 246.40 | 453 | 267.97 |
| -42 | 83.19 | 20 | 107.93 | 82 | 132.20 | 144 | 156.01 | 206 | 179.37 | 268 | 202.28 | 330 | 224.74 | 392 | 246.75 | 454 | 268.31 |
| -41 | 83.59 | 21 | 108.32 | 83 | 132.59 | 145 | 156.39 | 207 | 179.74 | 269 | 202.64 | 331 | 225.10 | 393 | 247.10 | 455 | 268.66 |
| -40 | 83.99 | 22 | 108.72 | 84 | 132.98 | 146 | 156.77 | 208 | 180.12 | 270 | 203.01 | 332 | 225.46 | 394 | 247.46 | 456 | 269.00 |
| -39 | 84.40 | 23 | 109.11 | 85 | 133.36 | 147 | 157.15 | 209 | 180.49 | 271 | 203.38 | 333 | 225.81 | 395 | 247.81 | 457 | 269.35 |

RTD テーブル

DIN EN 60751 準拠のクラス B とクラス A

| 抵抗 vs 温度表 DIN EN 60751 準拠のクラス B とクラス A $\alpha = 0.00385$ (ITS-90 基準) | |
|--|--|
| $t \geq 0^\circ \text{C}:$ $R(t) = R_0 \cdot (1 + A \cdot t + B \cdot t^2)$ ここで $A = 3,9083 \cdot 10^{-3} \text{ } ^\circ \text{C}^{-1}$ $B = -5,775 \cdot 10^{-7} \text{ } ^\circ \text{C}^{-2}$ $R_0 = 100\Omega$ | $t < 0^\circ \text{C}:$ $R(t) = R_0 \cdot [1 + A \cdot t + B \cdot t^2 + C \cdot (t - 100^\circ \text{C}) \cdot t^3]$ $A = 3,9083 \cdot 10^{-3} \text{ } ^\circ \text{C}^{-1}$ $B = -5,775 \cdot 10^{-7} \text{ } ^\circ \text{C}^{-2}$ $C = -4,183 \cdot 10^{-12} \text{ } ^\circ \text{C}^{-4}$ $R_0 = 100\Omega$ |
| | クラス B: $dt = \pm(0.3 + 0.005 \cdot t)^\circ \text{C}$ |
| | クラス A $dt = \pm(0.15 + 0.002 \cdot t)^\circ \text{C}$ |

